



Ball and Roller Bearings

The CAD data of products is available on the NTN website. See our website for details.

TECHNICAL EXPLANATION CONTENTS

1. Classification and characteristics of rolling bearings A-4	4.4 Equivalent load A-41	9.2 Low-speed rotation and rapid acceleration/deceleration A-107	14.3 Shaft and housing accuracy A-149
1.1 Structure A-4	4.5 Bearing rating life and load calculation examples A-43	9.3 Oscillating applications A-107	14.4 Bearing permitted inclination/allowable alignment angle A-149
1.2 Classification A-4		9.4 Heat rating rotational speed A-108	
1.3 Characteristics A-8			
2. Bearing selection A-14			
2.1 Bearing selection flow chart A-14			
2.2 Type and characteristics A-16			
2.3 Selection of bearing arrangement A-17			
3. Load rating and life A-20			
3.1 Bearing life A-20			
3.2 Basic rating life and basic dynamic load rating A-20			
3.3 Adjusted rating life A-22			
3.4 Modified rating life A-24			
3.5 Machine applications and requisite life A-27			
3.6 Weibull distribution and life adjustment factor for reliability A-28			
3.7 Misalignment angle (installation error) and life A-29			
3.8 Clearance and life A-30			
3.9 Basic static load rating A-30			
3.10 Allowable static equivalent load A-31			
3.11 Allowable axial load A-31			
3.12 Review of basic dynamic load ratings A-33			
3.13 Bearing life calculation tool A-33			
4. Bearing load calculation A-34			
4.1 Load acting on shafts A-34			
4.2 Bearing load distribution A-39			
4.3 Mean load A-40			
5. Boundary dimensions and bearing number codes A-46			
5.1 Boundary dimensions A-46			
5.2 Bearing numbers A-48			
6. Bearing tolerances A-54			
6.1 Dimensional and rotational accuracy A-54			
6.2 JIS terms A-56			
6.3 Chamfer measurements and tolerance or allowable values of tapered bore A-70			
6.4 Bearing tolerance measurement methods A-72			
6.5 Geometrical product specifications (GPS) A-73			
7. Bearing fits A-75			
7.1 Resultant fits A-75			
7.2 The necessity of a proper fit A-75			
7.3 Fit selection A-76			
8. Bearing internal clearance and preload A-88			
8.1 Bearing internal clearance A-88			
8.2 Selection of internal clearance A-88			
8.3 Preload A-100			
8.4 Necessary minimum load A-104			
9. Allowable speed A-106			
9.1 Constant speed rotation A-106			
10. Friction and temperature rise A-109			
10.1 Friction A-109			
10.2 Temperature rise A-109			
10.3 Starting torque calculation A-110			
11. Lubrication A-111			
11.1 Purpose of lubrication A-111			
11.2 Lubrication methods and characteristics A-112			
11.3 Grease lubrication A-112			
11.4 Solid grease A-119			
11.5 Oil lubrication A-120			
12. External bearing sealing devices A-124			
13. Bearing materials A-128			
13.1 Raceway and rolling element A-128			
13.2 Cage A-131			
13.3 Rubber seal materials A-132			
13.4 Periphery of bearing (shaft, housing) A-132			
13.5 NTN bearings with prolonged life A-132			
13.6 Bearing fatigue analysis technique A-139			
14. Shaft and housing design A-146			
14.1 Fixing of bearings A-147			
14.2 Bearing fitting dimensions A-148			