

Wrist Joint Module i-WRIST™


CAT.No.6511/E




Approach workpieces from various angles!

Wrist Joint Module i-WRIST™

Model diagram of system components




Example configuration





- * Inquire separately for other configurations.
- * Components in red are supplied by NTN. Inquire separately for other components.
- * One dedicated console can control multiple devices.
- * By customer to arrange the end effector, user's controller, XYZRz stage and workpiece.



Compact design







Features

1 Approach target positions from various angles!

- Wide operating range: maximum bend angle 90°, swing angle 360° (free)
- Coordinated operation combining the XYZ stage and rotation (Rz) stage.
- Compact layout.

2 Outstanding productivity!

- Able to move to a specified point in the quickest time.
- Equipped with automatic speed calculation algorithm (vibration suppression when stabilized).
- Layout with end effector mounted within link mechanism.


3 Quick changeover time and adjustments!

- Intuitive and easy-to-use dedicated console.
- Cables routed within link mechanism.
 (prevents cables becoming twisted after repeated swing motions)
- Save multiple operating patterns.

Main operation setting functions

Intuitive teaching process based on XYZ coordinates.

Fine adjustment of the position using jog button.






JOG operation screen

Enter XYZ coordinates and approach direction directly.





Coordinates input screen

- Operating conditions, motor gain and other settings can be configured.
- "JOB code" can be output to user's controller for each position, Using this "JOB code" users can set operations for each position with user's controller.
- Data of registered points can be edited and saved on a PC.



■ Liquid dispensing (grease, adhesive)





- Appearance inspections at more than 7 points per second is possible (depending on size of workpiece).
- •Inspect an entire hemispherical surface with a single camera.
- ■Cooperative control of compact layout combined with XYZRz stage.
- Other applications: welding, coating, cleaning, assembly, etc.

Specifications

Item	Content				
Wrist Joint Module i-WRIST™			90° bend angle type	45° bend angle type	
	Size (W×D×H)			331 × 286 × 202mm	388 × 335 × 191mm
	Mass (kg)			5.4	8.0
	Degrees of freedom			2	
	Operating range	Bend angle (°)		90	45
		Swing angle (°)		360 (free*1)	
	Weight capacity (kg)		1.0		
	Repeated positioning accuracy (°		acy (°)	±0.05	
	Control mode			PTP (Point to point) control, continuos pass control	
Dedicated controller	Size : W65 × D110 × H130 mm Attached unit : I/O unit (input: 32 points, output: 32 points) Rated voltage : DC 24 V ±20% Controlled object*2 : i-WRIST™ X stage, Y stage, Z stage, Rz stage (up to 4 axes)				
Dedicated console*3	Display device : Co Rated voltage : Do Mass : 0.		: Cold : DC : 0.96	W115.2 × L86.4 mm Color LCD DC 24 V ±20% D.96 kg or less 50 patterns (1 pattern: 100 points)	
External interface	Parallel input/output		EM JO : outp	input signals EMG stop, Reset, Break, Console ON, Enable SW, Start, Pause, JOB complete, CHG Pattern No., DATA 0 to 6, Servo OFF output signals Error, Ready, Busy, Complete, Move complete, Low battery, Reset, Pattern No. complete, DATA 0 to 6, Point 0 to 6, Trigger, JOB Code	

- *1: Swing operations can be repeated in the same direction.
- *2: Inquire separately for control target stage configurations.
- *3: One dedicated console can control multiple devices with same specifications.

What is i-WRIST™

"i-WRIST" is NTN Trade Mark created from combination of "i" (intelligent, innovative, interesting) and "WRIST" (referring to a human wrist).

